



YSHG3931

by Burndy
Catalog ID: YSHG3931

Prop 65 Notice

Copper Compression Double H- Tap Connector, 4/0 - 1/0 AWG (Tap 1)/ 1 - 6 AWG (Tap 2)/ 2 -14 AWG (Tap 3), # 6 Rebar/ 1" Cu Clad Rod/ 3/4" Ground Rod.

Features: UL467 Listed: Suitable For Direct Burial In Earth Or Concrete, Material Is High Conductivity Copper Extrusion: Minimizes Resistance, Eliminates Corrosion Due To Dissimilar Metals, Grooves Are Prefilled With PENETROX E2 Oxide Inhibitor And Individually Sealed: Inhibits Moisture And Contaminants Ensuring Electrical Integrity, Rebar Size: #6, Ground Rod Size: 1 IN, Die Index: KR Element A, Wire Entry: Double, Tools, Die Set Catalog Number, And (number Of Crimps): Y46 Tool, PYFR Die, (2), Conductor Type: Run: Rebar, Ground Rod, Copper Conductor, Tap1: Copper Wire, Tap2: Copper Wire, Tap3: Copper Wire, Conductor Size (run - Range): 350 - 500 KCMIL, Shape: H, Conductor Size (tap Range): Tap1: 1/0 - 4/0 AWG, Tap2: 6 - 1 AWG, Tap3: 14 - 2 AWG

Product Details

General

Application	For Direct Burial In Earth Or Concrete
Connector Type	H-Tap
Die Index	KR
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	HYGROUND®
Type	Taps
UPC	781810129685
UPC 12 Digit	7818101296855

Dimensions

Dimension - Length Overall inch	2.34 in
Dimension - Width inch	2.97 in
Dimension - Width mm	75 mm

Conductor Related

Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250-500 kcmil
Conductor - Copper Str Tap	4/0 - 1/0 AWG (Tap 1)/ 1 - 6 AWG (Tap 2)/ 2 -14 AWG (Tap 3)
Conductor - Copper Str Tap Range	4/0 - 1/0 AWG (Tap 1)/ 1 - 6 AWG (Tap 2)/ 2 -14 AWG (Tap 3)
Conductor - Rebar Run	6
Conductor - Rebar Run Range	6
Conductor - Rod Run	3/4 in

Conductor - Rod Run Range	3/4 in
---------------------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 467, Direct Burial
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)