



YSR29FX28LTCKITC

by Burndy
Catalog ID: YSR29FX28LTCKITC

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A:4/0 AWG(Flex-Str) Barrel B:4/0 AWG(Str), Standard Barrel, Electro-Tin Plated

Product Details

General

Color Code - Side A	Yellow
Color Code - Side B	Purple
Connector Type	Reducer;Splice
Die Index - Element A	16
Die Index - Element B	15
Die Index Run Side	16
Die Index Tap Side	15
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
UPC	781810415825
UPC 12 Digit	7818104158255

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.44 in
Dimension - L Length Overall mm	76 mm
Dimension - Length BB inch	1.30 in
Dimension - Length Overall inch	3.00 in
Dimension - Strip Length inch	1.38 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex I Size A	4/0 AWG
----------------------------------	---------

Conductor - Copper Flex K Size A	4/0 AWG
Conductor - Copper Flex M Size A	4/0 AWG
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)