

# YSS2R

by Burndy  
Catalog ID: YSS2R

Prop 65 Notice

Single aluminum sleeve designed for service drop or short span overhead distribution lines, Die index: BG or 5/8.

Features: Single Aluminum Sleeve Designed For Service Drop Or Short Span Overhead Distribution Lines, Installed With OH25 One-Hand Tool, And Other Standard Tooling, Pre-Filled With PENETROX Joint Compound And Color Coded Capped, Oh25 Application: Conductor, (indentd Per End): ACSR: 2 AWG (6-1), (7-1), (3), Aluminium: 2 AWG (7), (3), Holding Strength: ACSR: 1600 LB, Aluminum: 1200 LB, Die Index: BG Element A, Color Code: Red, Conductor Type: ACSR, Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W-BG Die, (3), BG Die, (6), Y35, Y750 Tool, U-BG Die, (3), Y45 Tool, U-BG Die With PT-6515 Adapter, (3), Y46 Tool, U-BG Die With PUADP-1 Adapter, (3)



## Product Details

### General

|                           |   |
|---------------------------|---|
| Application               | For Aluminum, ACSR, 6201, 5005 And Compressed Conductors And Service Drop Or Short Span Overhead Distribution Lines |
| Color Code                | Red   |
| Connector Type            | Splice  |
| Die Index                 | BG or 5/8   |
| Material                  | Aluminum  |
| Plated                    | N   |
| Plating Type              | Unplated  |
| Prefilled Oxide Inhibitor | Y   |
| Sub Brand                 | HYSPLICE  |
| Trade Name                | HYSPLICE™   |
| Type                      | YSS   |
| UPC                       | 781810169551  |
| UPC 12 Digit              | 7818101695511   |

### Dimensions

|                                   |            |
|-----------------------------------|------------|
| Dimension - B Length fraction     | 1-39/50 in |
| Dimension - B Length inch         | 1.78 in    |
| Dimension - L Length Overall mm   | 96 mm      |
| Dimension - Length Overall inch   | 3.78 in    |
| Dimension - Outside Diameter inch | 0.65 in    |

### Conductor Related

|                                 |  |
|---------------------------------|--|
| Conductor - ACSR Str Size       | 2 (6/1) Sparrow AWG; 2 (7/1) Sparate AWG |
| Conductor - ACSR Str Size Range | 2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG  |
| Conductor - AL Str Size         | 2 AWG                                    |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)