

YSS6RG2

by Burndy
Catalog ID: YSS6RG2

Prop 65 Notice

Single aluminum sleeve designed for service drop or short span overhead distribution lines, Die index: BG.

Features: Single Aluminum Sleeve Designed For Service Drop Or Short Span Overhead Distribution Lines, Installed With OH25 One-Hand Tool, And Other Standard Tooling, Pre-Filled With PENETROX Joint Compound And Color Coded Capped, Holding Strength: ACSR: 900 LB, Aluminum: 700 LB, Die Index: BG Element A, Conductor Type: ACSR, Aluminum, Color Code: Blue, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W-BG Die, (3), BG Die, (6), Y35, Y750 Tool, U-BG Die, (3), Y45 Tool, U-BG Die With PT-6515 Adapter, (3), Y46 Tool, U-BG Die With PUADP-1 Adapter, (3)



Product Details

General

Application	For Aluminum, ACSR, 6201, 5005 And Compressed Conductors And Service Drop Or Short Span Overhead Distribution Lines
Color Code	Blue
Connector Type	Splice
Die Index	BG
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YSS
UPC	781810169759
UPC 12 Digit	7818101697599

Dimensions

Dimension - B Length fraction	1-39/50 in
Dimension - B Length inch	1.78 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - AAAC 5005 Size	30.58 (7) kcmil
Conductor - AAAC 5005 Size Range	30.58 (7) kcmil
Conductor - AAAC 6201 Size	30.58 (7) kcmil
Conductor - AAAC 6201 Size Range	30.58 (7) kcmil
Conductor - ACSR Str Size	6 (6/1) Turkey AWG

Conductor - AL Str Size	4 AWG
-------------------------	-------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)