



YST2929

by Burndy
Catalog ID: YST2929

Prop 65 Notice

UNINSULATED HIGH VOLTAGE COPPER COMPRESSION SPLICE
STANDARD BARREL-TAPERED ENDS.

Product Details

General

Color Code	Yellow
Color Code - Side A	Yellow
Color Code - Side B	Yellow
Connector Type	T-Connector
Die Index	16
Die Index Run Side	16
Die Index Tap Side	16
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYTEE™
UPC	781810502037
UPC 12 Digit	7818105020377

Dimensions

Dimension - A Outside Diameter inch	0.75 in
Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - B Outside Diameter inch	0.75 in
Dimension - Height inch	2.53 in
Dimension - L Length Overall mm	108 mm
Dimension - Length BB inch	1.78 in
Dimension - Length Overall inch	4.25 in
Dimension - Width inch	1.78 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	250 kcmil
Conductor - Copper Str Run Range	250 kcmil
Conductor - Copper Str Tap	250 kcmil
Conductor - Copper Str Tap Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)