



YST2C2C

by Burndy
Catalog ID: YST2C2C

Prop 65 Notice

Cu compression T-Coupler, 2 str(Run&Tap), 600V-35Kv, Tin plated, Brown,10 index.

Features: Manufactured From Seamless High Conductivity Electrolytic Copper Tubing With Heavy Duty Wall Thickness, Long Barrel Design On All Three Legs, Long Barrel Permits The Use Of The Y-R Reducers, Electro-Tin Plated, Barrel Diameter Closely Matches Commercial (Code) Cable And Navy Cable Diameters, Color Code: Brown For Run, Brown For Tap, Tools, Die Set Catalog Number, And (number Of Crimps): Run And Tap: Y35, Y39, Y750 Tool, U2CRT Die, (2), Y46 Tool, U2CRT Die With PUADP-1 Adapter, (2), Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Mechanical HYTOOL: MY29-3, MY29-11 Tool, (2), MD6, MD7 Tool, (4), Hydraulic HYPRESS: Y644HS Tool, (1), Die Index: 10, Wire Strip Length: 1-5/16 IN Run And Tap

Product Details

General

Application	For Run Conductor With A Perpendicular Tap Conductor
Color Code	Brown
Color Code - Side A	Brown
Color Code - Side B	Brown
Connector Type	T-Connector
Die Index	10
Die Index Run Side	10
Die Index Tap Side	10
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYTEE
Temperature Rating	194
Trade Name	HYTEE™
Type	YST, Uninsulated T
UPC	781810501108
UPC 12 Digit	7818105011088

Dimensions

Dimension - A Outside Diameter inch	0.42 in
Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - B Outside Diameter inch	0.42 in
Dimension - Height inch	1.98 in
Dimension - L Length Overall mm	90 mm

Dimension - Length BB inch	1.56 in
Dimension - Length Overall inch	3.56 in
Dimension - Width inch	1.50 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	2 AWG
Conductor - Copper Str Run Range	2 AWG
Conductor - Copper Str Tap	2 AWG
Conductor - Copper Str Tap Range	2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)