

YST3131

by Burndy
Catalog ID: YST3131

Prop 65 Notice

UNINSULATED HIGH VOLTAGE COPPER COMPRESSION SPLICE
STANDARD BARREL-TAPERED ENDS.



Product Details

General

Color Code	Red
Color Code - Side A	Red
Color Code - Side B	Red
Connector Type	Tap
Die Index	18;324
Die Index Run Side	18
Die Index Tap Side	18
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYTEE™
UPC	781810502051
UPC 12 Digit	7818105020511

Dimensions

Dimension - A Outside Diameter inch	0.88 in
Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - B Outside Diameter inch	0.88 in
Dimension - Height inch	3.12 in
Dimension - L Length Overall mm	140 mm
Dimension - Length BB inch	2.25 in
Dimension - Length Overall inch	5.50 in
Dimension - Width inch	2.25 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	350 kcmil
Conductor - Copper Str Run Range	350 kcmil
Conductor - Copper Str Tap	350 kcmil
Conductor - Copper Str Tap Range	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)