



YST3428

by Burndy
Catalog ID: YST3428

Prop 65 Notice

UNINSULATED HIGH VOLTAGE COPPER COMPRESSION SPLICE
STANDARD BARREL-TAPERED ENDS.

Product Details

General

Color Code - Side A	Brown
Color Code - Side B	Purple
Connector Type	Tap
Die Index Run Side	20
Die Index Tap Side	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYTEE™
UPC	781810502068
UPC 12 Digit	7818105020688

Dimensions

Dimension - A Outside Diameter inch	1.06 in
Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - B Outside Diameter inch	0.69 in
Dimension - Height inch	2.81 in
Dimension - L Length Overall mm	148 mm
Dimension - Length BB inch	1.75 in
Dimension - Length Overall inch	5.81 in
Dimension - Width inch	1.75 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	500 kcmil
Conductor - Copper Str Run Range	500 kcmil
Conductor - Copper Str Tap	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)