

YSU25R25R

by Burndy
Catalog ID: YSU25R25R

Prop 65 Notice

Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code: Yellow (Side A), Yellow (Side B).

Features: Heavy-Walled Aluminum Tubing With Solid Barrier Minimizes Galvanic Corrosion Of Conductors, Accommodates Neutral Strands Of Type SE Service Entrance Conductor As Well As Other Conductors, Installed With Standard Tooling, Color Coded, Pre-Filled With PENE TROX Joint Compound And Stripsealed, Die Index: BG Element A, Conductor Type: Side A And Side B: ACSR, Aluminum, Copper, Tools, Die Set Catalog Number, And (number Of Crimps): HYTOOL: OH25 Tool, (1), MD6, MD7 Tool, (3), MD6, MD7 Tool, W-BG Die, (1), OUR840 Tool, X-NBG Die, (1), HYPRESS: Y35 Tool, U-BG Die, (1), Y35L, Y750 Tool, Color Code: Yellow (Side A And B)



Product Details

General

Application	For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 and Compressed Conductors
Color Code - Side A	Yellow
Color Code - Side B	Yellow
Die Index	243;BG or 5/8
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	LINKIT
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated, Center Stop
UPC	781810143988
UPC 12 Digit	7818101439888

Dimensions

Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - ACSR Str Size A	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	1/0 (6/1) Raven AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - Copper Str Size A	1/0 AWG

Conductor - Copper Str Size B	1/0 AWG
-------------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)