



YSV14NK

by Burndy
Catalog ID: YSV14NK

Prop 65 Notice

Copper Hylink, 20-14 AWG, 600 V-35 kV, 0.64" L, Nickel plated

Product Details

General

Connector Type	Splice
Die Index	36
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Shrouded
Material	Copper
Plated	Y
Plating Type	Nickel
Trade Name	HYLINK™
Type	Splice
UPC	781810080894

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.64 in
Dimension - Outside Diameter inch	0.16 in
Dimension - Strip Length inch	1/4 in

Electrical Ratings

Voltage - Maximum	35000 V
-------------------	---------

Conductor Related

Conductor - Copper Solid Size	12
Conductor - Copper Str Aircraft Size	AN 20;AN 18;AN 16;AN 14
Conductor - Copper Str Navy Size	2 1/2 (1);2 1/2 (19);2 1/2 (26);3 (7);4 (1);4 (7);4 (19);4 (41)
Conductor - Copper Str Size	20;18;16;14
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)