

YSV28FXB

by Burndy
Catalog ID: YSV28FXB

Prop 65 Notice

Hylink-Splice-Belled Long Barrel, 4/0 Str. (550/24) 4/0 AWG, 3.72 in L, UL Listed 90 Deg C, 600 Volts to 35 kV.

Features: Long Barrel Length: High Voltage Terminations, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Greater Mechanical And Electrical Properties, Belled Cable Entry: A Funnel Type Entry Provide Easy Insertion Of Extra Flexible Cables Plus Offers Mechanical Strain Relief For Individual Strands, Color Code: Purple, Tapered End: No, Oil Stop: No, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Die Index: 15 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750 Tool, U28RT Die, (4), Y46 Tool, U28RT Die With PUADP-1 Adapter, (4), Conductor Type: Flexible Copper, Wire Strip Length: 1-7/8 IN



Product Details

General

Application	For Higher voltage applications
Color Code	Purple
Connector Type	Splice
Die Index	15
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810041468

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.77 in
Dimension - D inch	0.90 in
Dimension - L Length Overall mm	94 mm
Dimension - Length Overall inch	3.72 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Strip Length inch	1-7/8 in

Conductor Related

Conductor - Copper DLO Size	4/0 (550/#24) DLO
Conductor - Copper Flex G Size	4/0 AWG

Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Str Compact Size	4/0
Conductor - Copper Str Compact Size Range	4/0
Conductor - Copper Str Navy Size	200 (61)
Conductor - Copper Str Size	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)