

YTS438E

by Burndy
Catalog ID: YTS438E

Prop 65 Notice

Full tension aluminum splice for EHS steel guy, messenger or "static" cable. ANSI C119.4 Class 1 (Full Tension), 12.32" L



Product Details

General

Connector Type	Splice
Die Index	726
Material	Aluminum Alloy
Trade Name	HYSPLICE™
UPC	781810016190
UPC 12 Digit	7818100161900

Dimensions

Dimension - L Length Overall mm	313 mm
Dimension - Length Overall inch	12.32 in

Conductor Related

Conductor - Galvanized Steel Str Size	7/16 (7) in
---------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)