



YTU33R28R

by Burndy
Catalog ID: YTU33R28R

Prop 65 Notice

1-piece heavy wall AL compression tap connector for secondary service drop and transformer tap to primary or secondary, 8-5/8 IN L

Product Details

General

Connector Type	Tap
Die Index Run Side	M
Die Index Tap Side	L
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810155950
UPC 12 Digit	7818101559500

Dimensions

Dimension - B Length inch	1.93 in
Dimension - Height inch	4 in
Dimension - L Length Overall mm	226 mm
Dimension - Length Overall inch	8.89 in

Conductor Related

Conductor - ACSR Str Run	336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Run Range	336.4 (30/7) Oriole kcmil-397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Tap	4/0 (6/1) Penguin AWG
Conductor - AL Str Run	397 kcmil;400 kcmil
Conductor - AL Str Run Range	397 kcmil-400 kcmil
Conductor - AL Str Tap	4/0 AWG
Conductor - Copper Str Run	400 kcmil
Conductor - Copper Str Tap	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)