

YTW36R362REKNT

by Burndy
Catalog ID: YTW36R362REKNT

Single Pad Full Tension Deadend for ACSR Conductor.



* Representative image

Product Details

General

| | |
|----------------|---------------|
| Connector Type | Deadend |
| Die Index | 721 |
| Material | Aluminum |
| UPC | 781810549735 |
| UPC 12 Digit | 7818105497355 |

Dimensions

| | |
|---------------------------------|----------|
| Diameter - Conductor Outside | 0.846 in |
| Dimension - B Length inch | 2.50 in |
| Dimension - Hole Size inch | 0.88 in |
| Dimension - L Length Overall mm | 496 mm |
| Dimension - Length Overall inch | 19.53 in |
| Dimension - Pad Width inch | 2.25 in |
| Thickness - Pad | 0.50 in |

Conductor Related

| | |
|---------------------------|-------------------------|
| Conductor - ACSR Str Size | 477(24/7) Flicker Kcmil |
|---------------------------|-------------------------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | UI |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)