

YTW43R43REKHT

by Burndy
Catalog ID: YTW43R43REKHT

Prop 65 Notice

Single Pad Full Tension Compression Deadend for ACSS Conductor



Product Details

General

Connector Type	Deadend
Feature - Barrel Style	Tapered
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810517161
UPC 12 Digit	7818105171611

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.88 in
Dimension - Length Overall inch	24.49 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	0.69 in

Conductor Related

Conductor - ACSS Str Size	605 (24/7) kcmil;605 (26/7) kcmil;605 (30/7) kcmil;605 (30/19) kcmil;636 (20/7) kcmil;636 (22/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;636 (30/7) kcmil;636 (30/19) kcmil;666.6 (24/7) kcmil
Conductor - ACSS Str Size Range	605 (24/7) kcmil-666.6 (24/7) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)