

YTW48RT481REKHT

by Burndy
Catalog ID: YTW48RT481REKHT

Full Tension, ACSS EHV Deadend Kits, Hardware TMH24, RUDDY 900 (45/7) kcmil, RAIL 954 (45/7) kcmil, YTW48RT481REKHTNT Aluminum Dead End Assy., BYNA49RT15HHT Terminal



Product Details

General

Application	For 250 Deg C. rated ACSS transmission lines, Corona free operation up to 230 KV
Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810491140
UPC 12 Digit	7818104911400

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Hole Size inch	1.25 in
Dimension - Length Overall inch	29.50 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	0.75 in

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	900 (45/7) kcmil;900 (54/7) kcmil;954 (42/7) kcmil;954 (20/7) kcmil;954 (45/7) kcmil
Conductor - ACSS Str Size Range	900 (45/7) kcmil - 954 (45/7) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)