



YTW52RDT521REK

by Burndy
Catalog ID: YTW52RDT521REK

Double Pad Full Tension Deadend for ACSR Conductor

Product Details

General

Connector Type	Deadend
Die Index	728
Feature - Barrel Style	Tapered
Material	Aluminum
Material - Clevis	Steel
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	NEMA
Physical Attribute - Pad Orientation	15 Degree Angle
UPC	781810518465
UPC 12 Digit	7818105184655

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	801 mm
Dimension - Length Overall inch	31.55 in
Dimension - Pad Width inch	4.00 in

Conductor Related

Conductor - ACSR Str Size	1192.5 (45/7) Bunting kcmil;1351.5 (45/7) Dipper kcmil
---------------------------	--

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)