



Z2929

by Burndy
Catalog ID: Z2929

Prop 65 Notice

Split Cone, Tubing Brass, 250 kcmil, 0.91" L, 0.78" - 0.66" Dia.

Product Details

General

Connector Type	Cone
Material	Brass
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810017418
UPC 12 Digit	7818100174188

Dimensions

Dimension - Cross Flats inch	0.94 in
Dimension - Length Overall inch	0.91
Length	0.91 in

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)