



Z3434

by Burndy
Catalog ID: Z3434

Prop 65 Notice

Split Cone, 500 Kcmil, 1.26 in L, Tin Plated.

Features: For Use With Socket And Nut Assembly, The Z Cone Is Machined To Close Tolerances To Provide Maximum Secureness In Gripping A Wide Range Of Cable Sizes, Annular Grooves In The Inner Barrel Of The Cone Serve To Further Accomplish This Result

Product Details

General

Application	For Use With Socket And Nut Assembly: Z34NR And 34NRB
Connector Type	Cone
Material	Brass
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	MOLE
Type	Z-MOLE
UPC	781810017425
UPC 12 Digit	7818100174255

Dimensions

Dimension - Length Overall inch	126
Length	1.26 in

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)