



Z34NR

by Burndy
Catalog ID: Z34NR

Prop 65 Notice

Socket And Nut Assembly, 500 kcmil, 5/8-18, 3-11/16 in L, Tin-Plated.

Features: Designed For Use With BURNDY Moles, With The Use Of The Proper Compression Cones, 14 Sizes Take A Range Of Cables From Number 6 To 1000 KCMIL, Their Compact Design Lends Them To Easy Effective Taping, Insulating Sleeves Are Available To Keep Taping To A Minimum, Uses Insulating Sleeve Z88C3429, Outlet Size: 6 AWG Stranded - 600 KCMIL, Stud Size: 5/8-18

Product Details

General

Application	Designed for use with Burndy mole
Connector Type	Nut
Installation Torque Recommended in-lb	450 lb-in
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	MOLE
Type	Z-NR
UPC	781810821220
UPC 12 Digit	7818108212200

Dimensions

Dimension - B Length fraction	17/32 in
Dimension - Cross Flats inch	1.50 in
Dimension - Length Overall inch	3.69
Weight	1.2 lb

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)