

Z40NRA

by Burndy
Catalog ID: Z40NRA

Prop 65 Notice

SOCKET AND NUT ASSEMBLY



Product Details

General

Connector Type	Nut
Installation Torque Recommended in-lb	450 lb-in
Insulation Type	Rubber
Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810081792
UPC 12 Digit	7818100817922

Dimensions

Dimension - B Length fraction	17/32 in
Dimension - Cross Flats inch	1.81 in
Dimension - Length Overall inch	5.53
Dimension - Width inch	3.83 in
Weight	2.4 lb

Conductor Related

Conductor - Copper Str Size	800 kcmil
Conductor - Copper Str Size Range	800 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)