



## BIBD2/03FX

by Burndy  
Catalog ID: BIBD2/03FX

Prop 65 Notice

UNITAP, double Sided Entry, #10-250 Class B & C ,#10-3/0 Class G,H,I,K, DLO, Aluminum.

Features: Clear Plastisol covered AL6061-T6 aluminum body, Saves time, lowers installation costs, eliminates taping, Oxide inhibitor pre-installed, Inhibits moisture and contaminants from entering the contact area

## Product Details

### General

|                    |   |
|--------------------|---|
| Application        | Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors |
| Insulation         | Y   |
| Material           | Aluminum  |
| Plated             | N   |
| Plating Type       | Unplated  |
| Sub Brand          | UNITAP  |
| Temperature Rating | 194   |
| Trade Name         | UNITAP™   |
| Type               | BIBD, Multi-Port  |
| UPC                | 621945438781  |
| UPC 12 Digit       | 6219454387811   |

### Electrical Ratings

|                          |     |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

### Conductor Related

|                |  |
|----------------|--|
| Conductor Type | <ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul> |
|----------------|--|

### Certifications and Compliance

|                                    |              |
|------------------------------------|--------------|
| Certification - CSA Approved       | Yes          |
| Industry Standard(s)               | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM           |
| UL Listed                          | Yes          |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)