

PAT444ST3U05A2

by Burndy
Catalog D: PAT444ST3UOSA2



- PATRIOT®T3 Technology 11-Ton Dieless Battery Crimper, C-Head, Uncovered, two 5.0Ah 18V Li-Ion Batteries, 120V-AC Charger, Hard Case
- TRACK crimp locations with onboard GPS - BURNDY ExclusFet
 - TRACE individual crimps with comments, photos, and output force validation
 - TRANSMIT via Bluetooth® technology and sync data to the cloud
 - C-Head for easy access and increased flexibility
 - Dieless System with range taking capability
 - Bright LED worklight and Red/Green LED to validate output force
 - Improved ergonomic design with more balance and better grip to reduce user fatigue
 - Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Product Details

General

Application	Crimping
Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads

Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita U Batteries)
Container Type	Hard Case
Crimp Force Capacity	11ton
Die Type	Dieless
Power Source	120V-AC Charger
Tool Type	Battery
Type	Crimper
UPC	621945624597

Dimensions

Dimensions	14.95 in x 3.25 in x 16.9 in
Height	16.9 in
Length	14.95 in
Weight	32.5 lb
Width	3.25 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 kcmil; Aluminum: #4 AWG - 1000 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	--

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)