



PATCUT1500LCB

by Burndy
Catalog ID: PATCUT1500LCB

Prop 65 Notice

PATCUT1500 LESS CHARGER and BATTERY

- Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- EP Enhanced Power tools accept 2.0, 3.0, 4.0, 5.0, and 6.0Ah Makita batteries

For Use On: Copper (hard drawn) up to 750 kcmil

Product Details

General

Application	Cutting
Battery Type	Multi Ah Capability Li Batteries
Sub Brand	Cable cutter
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	621945541184

Dimensions

Height	15.5 in
Length	6 in
Width	4.38 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Soft drawn copper: 1000 Kcmil; Aluminum: 1500 Kcmil
-----------------	---

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)