



## PATRIOTKIT2

by Burndy  
Catalog ID: PATRIOTKIT2

Prop 65 Notice

PATRIOT® Combo Kit Includes: PAT444S 11-Ton Dieless C-Head Crimper, PATCUT1500 CU/AL Ratchet Cutter, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, (2) Lanyards, Heavy Duty Hard Case

- CRIMPER: C-Head, Dieless system with range taking capability
- #4 -1000 kcmil Cu & Al,#4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation
- 11 ton output force
- Ergonomically balanced tool design
- CUTTER: Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- TOOLS: Accept 2Ah-6Ah 18V Makita lithium-ion batteries
- KIT: Packed in a heavy duty hardcase with custom foam and secure latches.

CRIMPER: C-Head, Dieless system with range taking capability;#4 -1000 kcmil Cu & Al,#4 - 556.6 ACSR, ACAR, AAC, AAAC;355° Head Rotation; 11 ton output force;Ergonomically balanced tool design; CUTTER: Variable speed trigger;Forward/Reverse switch features a locking position;Large, strategically placed, non-skid bumper;LED Worklight; TOOLS: Accept 2Ah-6Ah 18V Makita lithium-ion batteries; KIT: Packed in a heavy duty hardcase with custom foam and secure latches.5 Year Limited Warranty on Crimper, 3 Year on Cutter (excluding blades), 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE®

## Product Details

### General

Application	Crimping & Cutting
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Crimp Force Capacity	11 ton
Die Type	Dieless
Recharge Time	0.5 h
Sub Brand	PATRIOT® Crimper & Cutter
Tool Type	Battery Actuated Crimper & Cutter
Trade Name	PATRIOT®
Type	Crimper & Cutter
UPC	621945560932
UPC 12 Digit	621945560932

### Dimensions

Height	9.9 in
Length	24.53 in
Weight	43 lb
Width	19.55 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Crimping: Copper: #4 AWG - 1000 Kcmil; Aluminum: 4-1000 Kcmil; ACSR: #4 AWG- 556.6 Kcmil; Cutting: Soft drawn copper: 1000 Kcmil; Aluminum: 1500 Kcmil
-----------------	--

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
Package Contents	Crimping tool, cutting tool, (2) 3Ah 18V li-ion batteries, AC charger, (2) lanyards and heavy duty hard case

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)