



PATRIOTKIT4

by Burndy
Catalog ID: PATRIOTKIT4

Prop 65 Notice

PATRIOT® Combo Kit Includes: PAT750 12-Ton C-Head Crimper, U-Die Kit for Copper, PATCUT1500 CU/AL Ratchet Cutter, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, (2) Lanyards, Heavy Duty Hard Case

- CRIMPER: True, one-handed operation for advance, retract, and hold
- 12 ton output force
- State of the art crimping head design, 360° head rotation
- Ergonomically balanced tool design
- DIES: Stainless Steel U-Die Kit and Case for Copper Connectors #6 AWG-750 kcmil (15 Sets), Color coded dies are for crimping YA,YS,YA-A and YS-A types of connectors, ranging from #6 AWG through 750 kcmil
- CUTTER: Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- TOOLS: Accept 2Ah-6Ah 18V Makita lithium-ion batteries
- KIT: Packed in a heavy duty hardcase with custom foam and secure latches.

CRIMPER: True, one-handed operation for advance, retract, and hold;12 ton output force;State of the art crimping head design, 360° head rotation;Ergonomically balanced tool design; DIES: Stainless Steel U-Die Kit and Case for Copper Connectors #6 AWG-750 kcmil (15 Sets), Color coded dies are for crimping YA,YS,YA-A and YS-A types of connectors, ranging from #6 AWG through 750 kcmil; CUTTER: Variable speed trigger;Forward/Reverse switch features a locking position;Large, strategically placed, non-skid bumper;LED Worklight; TOOLS: Accept 2Ah-6Ah 18V Makita lithium-ion batteries; KIT: Packed in a heavy duty hardcase with custom foam and secure latches.5 Year Limited Warranty on Crimper, 3 Year on Cutter (excluding blades), 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE®

Product Details

General

Application	Crimping & Cutting
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Die Type	U Die
Recharge Time	0.5 h
Sub Brand	PATRIOT® Crimper & Cutter
Tool Type	Battery Actuated Crimper & Cutter
Trade Name	PATRIOT®
Type	Crimper & Cutter
UPC	621945560956
UPC 12 Digit	621945560956

Dimensions

Height	9.9 in
Length	24.53 in
Weight	48.7 lb
Width	19.55 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Crimping: Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground rods: 1/2"-1" diameter; Cutting: Soft drawn copper: 1000 Kcmil; Aluminum: 1500 Kcmil
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Crimping tool, cutting tool, U-die kit for copper, (2) 3Ah 18V li-ion batteries, AC charger, (2) lanyards and heavy duty hard case

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)