



* Representative image

Anchor, PISA Rod, 1in X 3.5ft corrosion protection, 1in threads

by CHANCE Utility
Catalog ID: C1022061

Protected Pisa anchor rod 1" (25.4 mm) diameter, 3' 6" (1067 mm) long.

- Hot forged hex collar provides strong connection to anchor and eye
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod

Product Details

General

| | |
|------------------|--|
| Coating | Galvanized |
| Strength Note | Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength. |
| Tensile Strength | 36000 lb |
| Type | Power Installed Screw Anchor (PISA) |
| UPC | 096359008576 |

Dimensions

| | |
|--------------|-----------|
| Length | 42.000 in |
| Rod Diameter | 1.000 in |
| Weight | 9.820 lb |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 50 EA |
| Standard Package | 5 |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com