



C2-125

by CMC
Catalog ID: C2-125

Copper Splicers, manufactured from high strength pure electrolytic copper to insure both maximum strength and conductivity. Easy to install with screwdriver, wrench or pliers and reusable. Plain copper finish. Wire range : 2/0-1/0 AWG, For use with copper conductor only, UL listed and CSA certified. 90° C Rated (486B Listed). Length : 1.25 in

Product Details

General

Material	Copper
UPC	192663135844

Conductor Related

Conductor - Copper Str Size Range	2/0-1/0 AWG
-----------------------------------	-------------