



\* Representative image

# Rod, Expanding/Cross-Plate Anchor, 1-1/4in X 8ft Tripleye

by CHANCE Utility  
Catalog ID: C2000028

Expanding/Cross-Plate Anchor Rod 1.25" (31.7 mm) Diameter Rod, 8' (2438 mm) long with Tripleye.

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

## Product Details

### General

Coating	Galvanized
Eye Nut Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	58000 lb
Type	Anchor Rod
UPC	096359012344

### Dimensions

Length	96.000 in
Rod Diameter	1.250 in
Weight	34.300 lb

### Logistics

Pallet Quantity	25 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com