



* Representative image

Rod, Expanding/Cross-Plate Anchor protected tube 3/4in X 8ft Thimbleye

by CHANCE Utility
Catalog ID: C2000090

Expanding/Cross-Plate Anchor Rod 0.75" (19.1 mm) Diameter Rod, 8' (2438 mm) long with Thimbleye with protective plastic tube.

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

Product Details

General

Coating	Galvanized with plastic tube
Eye Nut Style	Thimbleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	23000 lb
Type	Anchor Rod
UPC	096359012559

Dimensions

Length	96.000 in
Rod Diameter	0.750 in
Weight	11.917 lb

Logistics

Pallet Quantity	50 EA
Standard Package	5

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com