



\* Representative image

# Rod, Expanding/Cross-Plate Anchor protected tube 1in X 10ft Thimbleye

by CHANCE Utility  
Catalog ID: C2000103

Expanding/Cross-Plate Anchor Rod 1" (25.4 mm) Diameter Rod, 10' (3048 mm) long with Thimbleye with protective plastic tube.

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

## Product Details

### General

Coating	Galvanized with plastic tube
Eye Nut Style	Thimbleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	36000 lb
Type	Anchor Rod
UPC	096359012689

### Dimensions

Length	120.000 in
Rod Diameter	1.000 in
Weight	26.019 lb

### Logistics

Pallet Quantity	50 EA
Standard Package	2

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com