



* Representative image

Anchor, Tool, Kelly Bar Adapter, 3.5in Square, 15,000 ft-lb rating

by CHANCE Utility
Catalog ID: C3031571

3.5" Square 15K Kelly bar Adapter.

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Kelly bar adapter has twelve holes for 5/8" bolts on a 75/8" bolt circle, comes with twelve 5/8" Grade 2 bolts, nuts & lockwashers and bent arm pin with coil lock
- Painted with green paint

Product Details

General

Bolt Grade	2
Kelly Bar Shape	Square
Number of Bolt Holes	12
Torque Rating	15000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359510062

Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Kelly Bar Adapter Inside Width	3.5 in
Kelly Bar Hole Distance to Flange	<ul style="list-style-type: none"> • 2 in • 4 in
Length	6.688 in
Weight	33.000 lb

Logistics

Standard Package	1
------------------	---

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com