



# Yoke, Deadend Compression

by CHANCE Utility  
Catalog ID: C4010095



\* Representative image

Used with Two-Pole Strain Carriers, these units grip compression sleeves over the compressed area, requiring no shoulder or adapter to pull against. Castings are heat treated aluminum. When used with 2" adjustable strain poles, this assembly is rated at 11,000 pounds maximum load. Designed specifically for use on extension links and extruded compression deadends. A swing up gate exposes the shoe area of the assembly to the load and must be closed before taking up tension. The assembly can be installed hot on aluminum sleeves crimped with compression dies. Complete with 4 interchangeable shoes: 24AH Shoes for 477 to 556.5 kcmil ACSR 30AH Shoes for 715 to 954 kcmil ACSR 36AH Shoes for 1192.5 to 1351.5 kcmil ACSR and Hot Line Extension Link for 3/4" and 1" dia. shank.

## Product Details

### General

Style	Two Pole Strain Carrier - Accessories
UPC	096359017448

### Dimensions

Weight	41.16 lb
--------	----------

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)