



Epoxiglas Three Rail Straight Ladder, 20'

by CHANCE Utility
Catalog ID: C4020119



* Representative image

The greater mechanical strength, and less deflection of the Chance Three Rail Ladder increases the efficiency of line workers when working in a tagged-out position. The third rail also provides for a convenient, centered, safetybelt-tie, and divides the ladder rung into natural positions for each foot placement. Specifications include: 2.5" center rail, capped on both ends- 2" side rails with 8" swivel hooks on the top and caps on the bottom end of the rail, 1.25" sanded rungs- steel tie rods top and bottom and pinned sleeves on outside rails for spliced ladders with a 15.5" center. Both straight and spliced ladder units are available.

Product Details

General

Style	Three Rail
UPC	096359243656

Dimensions

Length	240 in
Weight	173.46 lb

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com