



Epoxiglas Spliced Ladder, 2.5" X 12' Top Section

by CHANCE Utility
Catalog ID: C4020402



* Representative image

LADDER, 2.5X12' TOP W/8" HK, Chance Epoxiglas Spliced Ladders are available in combinations of up to 32 feet in 2.5" diameter side rails, all splices are interchangeable, thus offering a variety of total reach with a few ladder sections in more convenient transportation lengths. One-inch diameter steel rods, 8" in diameter, are arched to hook over structural shapes are furnished on all top section units. The hooks are complete with steel chains- larger hooks are available on special order. Heavy-duty Chance Epoxiglas Ladders, manufactured in short, easy-to-transport lengths, are joined with the Chance Rigid Ladder Splice to form an unshakable, rigid splice- two eye pins in each rail, with a klik pin in the end of each are supplied.

Product Details

General

Style	Spliced Ladder
UPC	096359243687

Dimensions

Length	144 in
Weight	74.48 lb

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com