



Insulated Ratchet Cable Cutter For 1000 kcmil A.A. / 500 kcmil Cu, 8'

by CHANCE Utility
Catalog ID: C4031383



RATCHET WIRE CUTTER - 8FT - 1000AA+500CU, High-performance design incorporates Delrin plastic rollers and a two-piece operating rod. Roller mechanism travels smoothly along main Epoxiglas® pole. Linked through the roller support unit, the hinged operating rod and larger Epoxiglas pole reinforce each other. These Ratchet Cable Cutters meet OSHA Electrical Rating subpart V-section 1926.951 (d). Insulated support pole is Chance orange 112"-diameter Epoxiglas with Plastisol butt cap, operating shaft is 38"-diameter solid fiberglass rod, and lever handle is 1"-diameter Epoxiglas with rubber cushion grip.

* Representative image

Product Details

General

Storage Bag Included?	T306-0029 (Bag not included. Must be ordered separately.)
Type	Cutters
UPC	096359019060

Dimensions

Length	96 in
Weight	16.66 lb

Conductor Related

Conductor Size	1000 MCM A.A. / 500 MCM Cu.
----------------	-----------------------------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com