



Oh No!
IMAGE COMING SOON

15 kV By-Pass Jumper - 16', 1/0 Cable

by CHANCE Utility
Catalog ID: C6010261

INSULATED BY-PASS JUMPER - 15KV-1/0-16FT, A total of 16', the tool features mid-span an orange 8' epoxy-resin, rigid 1.5" fiberglass-reinforced-plastic (FRP) tube that serves as a support for easy handling of the jumper set by rubber gloves or hotline tools. Two non-metallic hangers-one at each end of the FRP support tube-provide for parking the by-pass clamps while moving the jumper set into or out of the work area. 4' of 1/0 cable extends from both ends of the rigid support.

Product Details

General

Torque Rating	250 in-lbs
UPC	096359024798

Dimensions

Jaw Opening Size - Maximum	1.5 in
Jaw Opening Size - Minimum	.162 in
Length - Jumper	192 in
Weight	21.609 lb

Electrical Ratings

Current Rating	260 A
Voltage Rating	15 kV

Conductor Related

Conductor Diameter (Main) - Maximum	1.5 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	1/0 AWG

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com