



\* Representative image

# 15 kV, 110 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination

by CHANCE Utility  
Catalog ID: C71EM112LBM

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 100A, 10kAIC fuseholder, large eyebolt connector and a NEMA "B" crossarm bracket.

## Product Details

### General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Description - Replacement Fuse Holder	T710-112TM
Type	Cutout
UPC	096359466215

### Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

### Logistics

Pallet Quantity	18 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com