

# 15/27 kV, 125 kV BIL, Type C Loadbreak Porcelain Cutout w/200A 10kAIC fuseholder

by CHANCE Utility  
Catalog ID: C730242PB

15/27 kV, 125 kV BIL, Loadbreak Type C Porcelain Cutout with a 200A, 10kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.



\* Representative image

## Product Details

### General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Description - Replacement Fuse Holder	T730-242T
Type	Cutout
UPC	096359244677

### Dimensions

Weight	28.048 lb
--------	-----------

### Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	40° C
Voltage - Radio Interference	36.2 micro-volts @ 15.66kV
Voltage Rating	15/27 kV

### Logistics

Pallet Quantity	24 EA
Standard Package	1

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)