



* Representative image

Clevis-Clevis

by ANDERSON
Catalog ID: CCC25

Clevis-Clevis, Ductile Iron, Clevis Openings 1.188" & 0.688", Clevis Pins 0.625", UTS 25,000 lb

Product Details

General

Coupling Orientation	Straight
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	CCC Series
Strength Rating - Ultimate	25000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359297079

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	3 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.450 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com