



Anchor, Lead, SS5, 8/10 X 7ft

By Chance
Catalog # 012642AE7

Square Shaft (SS 5) Lead Section 7' (2134 mm) long with 8" (203 mm) - 10" (254 mm) Helices.

Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Application

Helical Anchoring

General

Catalog Number	012642AE7
Coating	Galvanized, ASTM A-153
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	5500 ft-lbs

TypeLead Sections

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in
Length	84 in

Logistics

Standard Package	1
------------------	---

Product Assets

- Catalogs - Anchor Tools
- Catalogs - Anchors
- Catalogs - Dependable Anchoring Solutions
- Catalogs - Communications Catalog
- Installation Manuals - Holding Capacity Chart - SS5 Anchors
- Installation Manuals - TD06132E_Type_SS_and_RR_Anchors
- Installation Manuals - Holding Capacity Chart - Soil Classification
- Literature - Helical Piles and Guy Anchors Structures
- Literature - CHANCE Anchor Tool Inspection and Maintenance
- Specifications - 012642AE7
- Video - CHANCE Square Shaft Anchor Installation
- Video - CHANCE Square Shaft Anchor Tools Selection Process
- Video - Chance Foundation Solutions Anchor/Pile Installation Tools