



Anchor, Lead, SS5, 10 X 5.5ft

By CHANCE Utility
Catalog # [012642E](#)

Square Shaft (SS 5) Lead Section 5' (1524 mm) long with 10" (254 mm) Helix



Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Number of Helices	1
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	5500 ft-lbs
Type	Lead Sections
UPC	096359734093

Dimensions

Anchor Helix Diameter(s)	10 in
Length	60.000 in

Logistics

Standard Package	1
------------------	---

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

- [12655 - Anchor, Extension, SS5, X 3.5ft](#)
- [12657 - Anchor, Extension, SS5, X 7ft](#)
- [12658 - Anchor, Extension, SS5, X 10ft](#)
- [12656 - Anchor, Extension, SS5, X 5ft](#)



A proud member of the Hubbell Family.