



Anchor, PISA 4 10in, 5/8in threads

By CHANCE Utility
Catalog # [024476](#)



Standard Strength Anchor Helix.; 4,000 Ft Lbs (5,424 N-M),
10" (254 mm) Helix for use with 0.625" (15.9 mm) Rod.

Features

- Installed with Chance anchor wrench C1021583
- Anchor has curvilinear leading edges to help penetrate rocky soils and to reduce damage during installation
- 5/8" threads to fit 5/8" diameter Pisa rod
- Anchors are painted with a black paint

Application

Helical Anchoring

General

Coating	Painted
Number of Helices	1
Torque Rating	4000 ft-lbs
Type	Anchor Helix
UPC	096359209652

Dimensions

Anchor Helix Diameter(s)	10 in
Anchor Hub Size	1.375 in
Rod Diameter	0.625 in
Weight	13.994 lb

Logistics

Pallet Quantity	144
Standard Package	4

Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Installation Manuals - TD06131E_PISA_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors \(TD06166E\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - How to Match Anchors and Installing Wrenches \(049114\)](#)
- [Sales Drawings - Helix And Core Assembly \(SA10200000\)](#)
- [Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

Related Products

[C1021583 - Anchor, Tool, Drive End Wrench, Orange Band, rated 10,000 ft-lbs, 7ft long](#)



A proud member of the Hubbell Family.