



DISCONTINUED - Anchor, PISA 4, 12in, 1in threads

By Chance
Catalog # 024481

DISCONTINUED - Standard Strength Anchor Helix.; 4,000 Ft Lbs (5,424 N-M), 12" (304 mm) Helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

Features

- Replaced by E1021634
- Installed with Chance anchor wrench C1021583
- Anchor has curvilinear leading edges to help penetrate rocky soils and to reduce damage during installation
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

Application

Helical Anchoring

General

Catalog Number	024481
Coating	Painted
Number of Helices	1
Torque Rating	4000 ft-lbs
Type	Anchor Helix
UPC	096359209676

Dimensions

Anchor Helix Diameter(s)	12 in
Anchor Hub Size	1.375 in



Rod Diameter	<ul style="list-style-type: none">• 0.75• 1 in
Weight	16.503 lb

Logistics

Pallet Quantity	48
Standard Package	4

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Installation Manuals - TD06131E_PISA_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Sales Drawings - Helix And Core Assembly](#)
- [Specifications - 24481](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)