



Anchor, PISA Rod, Coupler 1in threads

By Chance
Catalog # [12247P](#)



Pisa anchor rod Coupling 3/4 & 1" (25.4 mm) diameter.

Features

- Hot dipped galvanized per ASTM A153
- Coupling fit 3/4" and 1" diameter Pisa rods that have 1" threads

Application

Helical Anchoring

General

Catalog Number	12247P
Coating	Galvanized, ASTM A-153
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	50000 lb.
Type	Power Installed Screw Anchor (PISA)
UPC	096359068242

Dimensions

Dimensions	2.000 in x 1.070 in x 1.070 in
Height	1.07 in

Length	2 in
Rod Diameter	<ul style="list-style-type: none">• 0.75• 1 in
Weight	0.48 lb
Width	1.07 in

Logistics

Pallet Quantity	4000
Standard Package	50

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Communications Catalog](#)
- [Installation Manuals - TD06131E_PISA_Anchors](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Sales Drawings - Coupling Nut](#)
- [Sales Drawings - Coupling Nut](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - 12247P](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand