



Anchor, PISA Rod, Extension w/coupler, 3/4in X 3.5ft, 1in threads

By Chance
Catalog # [12250A](#)

Pisa anchor rod 0.75" (19.1 mm) diameter, 3' 6" (1067 mm) long with coupling.



Features

- Hot forged hex collar provides strong connection to anchor and eye
- Hot dipped galvanized per ASTM A153
- Coupling assembled to rod
- Rods used with PISA® Power Installed Screw Anchors
- Cannot be used with Expanding and Plate Anchors

General

Application	Helical Anchoring
Catalog Number	12250A
Coating	Galvanized, ASTM A-153
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	23000 lb.
Type	Power Installed Screw Anchor (PISA)
UPC	096359068273

Dimensions

Length	42 in
Rod Diameter	0.75 in
Weight	5.635 lb

Logistics

Pallet Quantity	50
Standard Package	5

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06131E_PISA_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance Literature - Anchoring](#)
- [Sales Drawings - Pisa-Rod- Ext. With -Coupling](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand