



Anchor, PISA Rod, 5/8in X 7ft, 5/8in threads

By CHANCE Utility
Catalog # 12332P

Pisa anchor rod 0.625" (15.9 mm) diameter, 7' (2134 mm) long.



Features

- Hot forged hex collar provides strong connection to anchor and eye
- Hot dipped galvanized per ASTM A153
- Rods used with PISA® Power Installed Screw Anchors
- Cannot be used with Expanding and Plate Anchors

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	16000 lb.
Type	Power Installed Screw Anchor (PISA)
UPC	096359068341

Dimensions

Length	84.000 in
Rod Diameter	0.625 in
Weight	6.282 lb

Certifications and Compliance

RUS Listed Reference	z - Anchors, screw, power installed
----------------------	-------------------------------------

Logistics

Pallet Quantity	50
Standard Package	5

Product Assets

- [Catalogs - Anchors \(4\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)



A proud member of the Hubbell Family.