



# Anchor, PISA Rod, 5/8in X 3.5ft, 5/8in threads

By CHANCE Utility  
Catalog # [12336P](#)

Pisa anchor rod 0.625" (15.9 mm) diameter, 3' 6" (1067 mm) long.



\*Representative Image

### Features

- Hot forged hex collar provides strong connection to anchor and eye
- Hot dipped galvanized per ASTM A153
- Rods used with PISA® Power Installed Screw Anchors
- Cannot be used with Expanding and Plate Anchors

### Application

Helical Anchoring

### General

Coating	Galvanized, ASTM A-153
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	16000 lb.
Type	Power Installed Screw Anchor (PISA)
UPC	096359068365

### Dimensions

Length	42.000 in
Rod Diameter	0.625 in
Weight	4.410 lb

### Logistics

Pallet Quantity	50
Standard Package	5

### Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06131E\\_PISA\\_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Anchor Rod, Power Screw \(SA1020001\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

### Related Products

- [12589 - Anchor, PISA Nut, 5/8in threads, Twineye](#)
- [12593 - Anchor, PISA Nut, 5/8in threads, Tripleye](#)
- [12587 - Anchor, PISA Nut, 5/8in threads, Thimbleye](#)



A proud member of the Hubbell Family.