



# Anchor, PISA Nut 1in threads Tripleye

By CHANCE Utility  
Catalog # [12585](#)

Tripleye eyenut for 0.75" (19.1 mm) & 1" (25.4 mm) Pisa Rod.



\*Representative Image

## Features

- For use the Pisa style anchor rods
- Eyes are dropped forged for better strength and reliability
- Hot dipped galvanized per ASTM A153

## Application

Helical Anchoring

## General

Coating	Galvanized, ASTM A-153
Eyenut Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	<ul style="list-style-type: none"> <li>• 23000 lb.</li> <li>• 36000 lb.</li> </ul>
Type	Power Installed Screw Anchor (PISA)
UPC	096359068396

## Dimensions

Rod Diameter	<ul style="list-style-type: none"> <li>• 0.750</li> <li>• 1.000 in</li> </ul>
Weight	2.058 lb

## Logistics

Pallet Quantity	960
Standard Package	25

## Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06131E\\_PISA\\_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Nut, Tripleye \(SA12585\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

## Related Products

- [12334P - Anchor, PISA Rod, 1in X 7ft, 1in threads](#)
- [12632P - Anchor, PISA Rod, 3/4in X 7ft, 1in threads](#)
- [C2030148 - Tripleye® ANCHOR ROD BONDING CLAMP for 5/8in, 3/4in & 1in PISA RODS](#)



A proud member of the Hubbell Family.