



Anchor, PISA Nut, 5/8in threads, Thimbleye

By CHANCE Utility
Catalog # 12587



Thimbleye eyenut for 0.625" (15.9 mm) Pisa Rod.

*Representative Image

Features

- For use with Pisa style anchor rods
- Eyes are dropped forged for better strength and reliability
- Hot dipped galvanized per ASTM A153
- Not for use on 5/8" Machine Bolts

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Eyenut Style	Thimbleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	16000 lb.
Type	Power Installed Screw Anchor (PISA)
UPC	096359068419

Dimensions

Rod Diameter	0.625 in
Weight	0.853 lb

Certifications and Compliance

RUS Listed Reference	z - Anchors, screw, power installed
----------------------	-------------------------------------

Logistics

Pallet Quantity	1600
Standard Package	25

Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06131E_PISA_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Thimbleye Nut \(SA12587\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

Related Products

- [12332P - Anchor, PISA Rod, 5/8in X 7ft, 5/8in threads](#)
- [12336P - Anchor, PISA Rod, 5/8in X 3.5ft, 5/8in threads](#)
- [G5067 - Thimbleye® ANCHOR ROD BONDING CLAMP for 5/8in PISA RODS](#)



A proud member of the Hubbell Family.